



Ortronics F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras.

Features & Benefits

Low profile connector: Allows furniture to be placed closer to the wall.

75 Ohm F-connector: Ideal for cable and satellite TV, cable modems, and security cameras.

Rear loading module: Allows for termination before and during the construction process.

Designed for multiple coax cable styles: Accepts both push-style and screw-style.

TechChoice keystone footprint: Fits in all TechChoice faceplates and housings.

Integrates with Legrand Wiremold : Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

Specifications

General Info

Product Line	Ortronics	Color	Electrical Ivory
UPC Number	662875834755	Country Of Origin	Taiwan, Province Of China
Application Sector	Commercial, Industrial	Standard	UL Standard
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.55 in	Product Depth US	0.875 in
Product Height US	0.63 in		

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Frequency Rating	3 GHz	Connector 2	F-Type Male
Connector 1	F-Type Female	Impedance	75 Ohm