



Ortronics
DUAL GANG KEYSTONE FACEPLATE, 12 PORT, CLOUD WHITE
Part No. KSFP12-88



TechChoice faceplates are available in thermoplastic and stainless steel, with a variety of port capacities to match your workstation applications. All faceplates allow for a flush jack finish. For more information, please contact your local sales representative.

Features & Benefits

Low profile design: Supports most environments.

Field configurable with Keystone: Design or site flexibility for new or retrofit.

Recessed label fields: Supports TIA/EIA 606 standard.

Specifications

General Info

| | | | |
|--------------------|---------------------------|-----------------|--------------|
| Product Line | Ortronics | Color | Cloud White |
| Finish | Brushed | UPC Number | 662875595007 |
| Country Of Origin | Taiwan, Province Of China | Wall Plate Type | Networking |
| Application Sector | Commercial | Standard | UL Standard |
| Warranty Type | 5-Year | Type | Workstation |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 2.73 in | Product Depth US | 0.22 in |
| Product Height US | 4.5 in | | |

Additional Information

Product Environmental Profile Yes

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|-----------|
| Operating Temperature Min | -10 °C | Compatibility | Keystone |
| Number of Ports | 12 | Operating Temperature Max | 60 °C |
| Number of Gangs | 2 | Indoor/Outdoor | Indoor |
| Mounting Type | Box Mounted | Operating Temperature | -10°-60°C |
| Orientation | Vertical | | |