



Ortronics
DUAL GANG KEYSTONE FACEPLATE, 8 PORT, WM IVORY
Part No. KSFP8-99



TechChoice faceplates are available in thermoplastic and stainless steel, with a variety of port capacities to match your workstation applications. All faceplates allow for a flush jack finish. For more information, please contact your local sales representative.

Features & Benefits

- Low profile design: Supports most environments.
- Field configurable with Keystones: Design or site flexibility for new or retrofit.
- Recessed label fields: Supports TIA/EIA 606 standard.

Specifications

General Info

Product Line	Ortronics	Color	Ivory
Finish	Brushed	UPC Number	662875622994
Country Of Origin	Taiwan, Province Of China	Wall Plate Type	Networking
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Workstation

Dimensions

Product Width US	2.73 in	Product Depth US	0.22 in
Product Height US	4.5 in		

Additional Information

Product Environmental Profile Yes

Technical Information

Operating Temperature Min	-10 °C	Compatibility	Keystone
Number of Ports	8	Operating Temperature Max	60 °C
Number of Gangs	2	Indoor/Outdoor	Indoor
Mounting Type	Box Mounted	Operating Temperature	-10°-60°C
Orientation	Vertical		