



TechChoice faceplates are available in thermoplastic and stainless steel, with a variety of port capacities to match your workstation applications. All faceplates allow for a flush jack finish. For more information, please contact your local sales representative.

Features & Benefits

Recessed label fields: Supports TIA/EIA 606 labeling standard.

Specifications

General Info

| | | | |
|--------------------|---------------------------|-----------------|--------------|
| Product Line | Ortronics | Color | Fog White |
| Finish | Brushed | UPC Number | 662875534907 |
| Country Of Origin | Taiwan, Province Of China | Wall Plate Type | Networking |
| Application Sector | Commercial | Standard | UL Standard |
| Warranty Type | 5-Year | Type | Wall Plate |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 4.53 in | Product Depth US | 0.17 in |
| Product Height US | 4.5 in | | |

Additional Information

| | | | |
|-------------------------------|-----|---|-----|
| RoHS Compliant | Yes | Product Has Potential to Contribute to LEED | Yes |
| Product Environmental Profile | Yes | | |

Technical Information

| | | | |
|---------------------------|-----------|---------------------------|-----------|
| Operating Temperature Min | -10 °C | Compatibility | Keystone |
| Number of Ports | 2 | Operating Temperature Max | 60 °C |
| Number of Gangs | 2 | Indoor/Outdoor | Indoor |
| Mounting Type | Screwless | Operating Temperature | -10°-60°C |
| Orientation | Vertical | | |