



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase

## Features & Benefits

- Individual Patch Cable Assembly – Standard Insertion Loss: 0.30 dB Insertion loss
- Single-mode total channel connection loss: 2.1 dB
- Cable Size: All configurations below are 2mm duplex zipcord - other configuration options available
- Polarization: A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable
- Compliance: BAA or TAA
- Part of a Standard Loss System. When combined with Infinium Core Trunks and Infinium Core Cassettes
- Single-mode total channel connection return loss: 49 dB
- Fiber Type: Supports Single-Mode OS2 Fiber
- Jacket Color: Yellow - other configuration options available

## Specifications

### General Info

Product Line	Ortronics	Country Of Origin	United States
Type	Fiber Patch Cord		

### Dimensions

Product Length US	15.0 FT
-------------------	---------

### Technical Information

Jacket Application	Plenum Rated	Simplex/Duplex	Duplex
Jacket Rating	FT6 Rated, OFNP Rated		