



Turnlok® Single Receptacle, 3-Wire 30A 3-Phase 480V

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	1.61 in	Product Depth US	1.28 in
Product Height US	2.42 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Additional Information

---

Product Environmental Profile      Yes

---

## Technical Information

---

Phase	3	Number of Wires	3
Amperage	30 A	Number of Poles	3-Way
Wire Size	18 - 10 AWG	Voltage	480.0 V

---