



Pass and Seymour
20A 125/250V NEMA L1420 Single Receptacle, 4-Wire, Black
Part No. L1420R



Turnlok® Single Receptacle 4-Wire 20A 125/250V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007142051
Country Of Origin	Mexico	Number of Receptacles	1
Features	Brass Mounting Strap, Impact Resistant	Outlet Type	Locking
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 498, FDSPEC	Warranty Type	1-Year Limited Warranty
Type	Outlet		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Connection Location	Back and Side	Number of Wires	4
Amperage	20 A	Number of Poles	3-Way
Wire Size	4 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	L14-20R	Mounting Type	Box
Wire Connection Type	Screw Terminals	Voltage	125/250 V