



Pass and Seymour
30A NEMA L1430 Flanged Inlet, Gray
Part No. L1430FI



Flanged Inlet 4-Wire 30A 125/250V TurnLok®

Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007143027	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498

Dimensions

Product Width US	3.12 in	Product Depth US	1.75 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Number of Wires	3	Amperage	30 A
-----------------	---	----------	------

Number of Poles	Double Pole	Wire Size	4
-----------------	-------------	-----------	---
