

Turnlok® Flanged Inlet, 4-Wire 30A 250V



## Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

## Specifications

### General Info

|                   |                |                    |            |
|-------------------|----------------|--------------------|------------|
| Product Line      | Pass & Seymour | Color              | Gray       |
| Country Of Origin | Mexico         | Application Sector | Commercial |
| Standard          | UL 498         |                    |            |

### Dimensions

|                  |         |                  |         |
|------------------|---------|------------------|---------|
| Product Width US | 3.12 in | Product Depth US | 1.75 in |
|------------------|---------|------------------|---------|

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|          |      |                 |       |
|----------|------|-----------------|-------|
| Phase    | 3    | Number of Wires | 4     |
| Amperage | 30 A | Number of Poles | 3-Way |

---

Wire Size

18 - 10 AWG

Voltage

250.0 V

---