



Pass and Seymour
30 Amp NEMA L1530 Single Receptacle
Part No. L1530R

Turnlok Single Receptacle 4wire 30amp 3phase 250v



Features & Benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Accepts #14 - #10 AWG.
- Face color coding by voltage facilitates locating and mating of proper devices.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Color	Black	UPC Number	785007153057
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL 498

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Poles	Double Pole	Voltage	250 V
Wire Size	4 AWG	Number of Wires	3