



Connector 4-Wire 30A 600V Turnlok Registered

Features & Benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock. Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material. Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal. Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention. Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

| | | | |
|--------------|---------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| UPC Number | 785007173017 | Country Of Origin | Mexico |
| Features | Corrosion Resistant | Application Sector | Industrial |
| Standard | UL 498 | Warranty Type | 1-Year |
| Type | Connector | | |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 3.33 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------------|---------|---------|----|
| Connector Style | Locking | Flanged | No |
|-----------------|---------|---------|----|

| | | | |
|------------------------|-------------------|-----------------|---|
| Terminal Accommodation | #18 AWG - #10 AWG | Number of Wires | 4 |
|------------------------|-------------------|-----------------|---|

| | | | |
|----------|------|-----------------|-------|
| Amperage | 30 A | Number of Poles | 3-Way |
|----------|------|-----------------|-------|

| | | | |
|----------------|--------|-------------------------|---------|
| Indoor/Outdoor | Indoor | NEMA Configuration Code | L17-30R |
|----------------|--------|-------------------------|---------|

| | | | |
|------------------|---|---------|---------|
| Number of Phases | 3 | Voltage | 600.0 V |
|------------------|---|---------|---------|
