Pass and Seymour
20A 120/208V NEMA L2120 Single Receptacle, 5-Wire 3-Phase, Black
Part No. L2120R

Turnlok Registered Single Receptacle 5-Wire 20A 3-Phase 120/208V

Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007212051
Country Of Origin	Mexico	Product Type	Receptacle
Number of Receptacles	1	Features	Brass Mounting Strap, Impact Resistant
Outlet Type	Locking	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in	Circular Outlet Diameter	1.545 in

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes

Additional Information

Product Environmental Profile	Yes

Technical Information

Connection Location	Back and Side	Number of Wires	5
Amperage	20 A	Number of Poles	4-Way
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	L21-20R	Wire Connection Type	Screw Terminals
Voltage	120/208 V		