



Pass and Seymour  
20A 120/208V NEMA L2120 Single Receptacle, 5-Wire 3-Phase, Black  
Part No. L2120R

Turnlok® Single Receptacle 5-Wire 20A 3-Phase 120/208V



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007212051
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial, Industrial	Standard	UL 498, FEDSPEC
Type	Outlet		

### Dimensions

Product Width US	1.61 in	Product Depth US	1.19 in
Product Height US	2.29 in		

---

Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Additional Information

---

Product Environmental Profile	Yes
-------------------------------	-----

---

Technical Information

---

Amperage	20 A	Number of Poles	Double Pole
Wire Size	4 AWG	Indoor/Outdoor	Indoor

---