



Pass and Seymour  
20A NEMA Plug L2220 - Black Back, White Front Body  
Part No. L2220P

Plug 5-Wire 20A 277/480V Turnlok®



## Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007222043	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498
Type	Plug Tail		

### Dimensions

Product Width US	2.2 in	Product Length US	2.57 in
------------------	--------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Phase	Three	Number of Wires	5
Amperage	20 A	Number of Poles	4-Way
Wire Size	18 - 10 AWG		