



Pass and Seymour
30A L2230 Plug - Black Back, White Front Body
Part No. L2230P

Plug 5-Wire 30A 277/480V Turnlok®



Features & Benefits

| | |
|---------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity. |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock. | Double dovetail design provides superior protection against cord pull-out forces. |
| Impact- and corrosion-resistant durable nylon 6 shell material. | Rounded back contour reduces snags and hang-ups on the job site. |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal. | Visible stamped NEMA configuration and device rating. |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL 498 | Type | Plug Tail |

Dimensions

| | | | |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 2.57 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

| | |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

| | | | |
|-----------|-------------|-----------------|---------|
| Phase | 3 | Number of Wires | 5 |
| Amperage | 30 A | Number of Poles | 4-Way |
| Wire Size | 18 - 10 AWG | Voltage | 277.0 V |
