

Receptacle Single 5wire 30amp 347/600volt Turnlok



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Color	Black	UPC Number	785007233056
-------	-------	------------	--------------

Country Of Origin	Mexico	Product Line	Pass & Seymour
-------------------	--------	--------------	----------------

Application Sector	Commercial	Standard	UL 498
--------------------	------------	----------	--------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	140596
--------------	-----	---------------------	--------

### Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

### Technical Information

Number of Poles	4-Way	Voltage	347 V
-----------------	-------	---------	-------

Phase	3	Wire Size	10-18Awg
-------	---	-----------	----------

Number of Wires	5
-----------------	---