



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase.

Features & Benefits

Part of a Ultra- Low Loss System: When combined with Infinium Ultra Trunks and Infinium Ultra Cassettes	Flexible Polarity: A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable
Compliance: BAA or TAA Compliant	Bend-insensitive fiber for optimal cable management and ease of installation
Dust caps pre-installed	TIA Channel Compliant

Specifications

General Info			
Product Line	Ortronics	Country Of Origin	United States
Type	Fiber Patch Cord		
Dimensions			
Product Length US	15.0 FT		
Technical Information			
Fiber Optic Cable Type	OM4	Jacket Application	Plenum Rated
Simplex/Duplex	Duplex	Cable Type	Fiber Optic
Jacket Rating	FT6 Rated, OFNP Rated	Performance Level/Tier	Infinium Ultra