



Pre-Configured Infinium Fiber Patch Cords are built to exceed industry standards for quality, performance, insertion and return loss. Available in three performance tiers Infinium Quantum, Infinium Ultra, and Infinium Core. Each tier is available in Single-mode and Multimode. The most common configurations are setup for easy selection and purchase

Features & Benefits

Part of a Ultra – Low Loss System: When combined with Infinium Ultra Trunks and Infinium Ultra Cassettes

Compliance: BAA or TAA Compliant

Dust caps pre-installed

Flexible Polarity: A-B and is designed to pair with Infinium Universal Polarity Cassettes - Reconfigurable

Bend-insensitive fiber for optimal cable management and ease of installation

TIA Channel Compliant

Specifications

General Info

Product Line	Ortronics	Color	Yellow
Country Of Origin	Mexico	Type	Fiber Patch Cord

Dimensions

Product Length US	1.0 m	Cable Length	1 m
-------------------	-------	--------------	-----

Technical Information

Fiber Optic Cable Type	OS2	Jacket Application	Plenum Rated
Simplex/Duplex	Duplex	Cable Type	Fiber Optic
Jacket Rating	FT6 Rated, OFNP Rated	Performance Level/Tier	Infinium Ultra