



Pass and Seymour
20A NEMA Plug L2420 - Black Back, White Front Body
Part No. L3720P

Turnlok® Plug, 20A 347V, IP20 Suitability, L24-20P



Features & Benefits

- | | |
|---|--|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire. | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity. |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock. | Double dovetail design provides superior protection against cord pull-out forces. |
| Impact- and corrosion-resistant durable nylon 6 shell material. | Rounded back contour reduces snags and hang-ups on the job site. |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal. | Visible stamped NEMA configuration and device rating. |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007170047	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498

Dimensions

Product Width US	2.2 in	Product Length US	2.57 in
------------------	--------	-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Phase	Three	Number of Wires	3
-------	-------	-----------------	---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	18 - 10 AWG
-----------	-------------
