

Flanged Outlet 3-Wire 20A 125V Turnlok®



## Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498		

### Dimensions

Product Width US	2.87 in	Product Depth US	1.34 in
------------------	---------	------------------	---------

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	16063
------------	-----	-----------------	-------

### Technical Information

Phase	3	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole

---

Wire Size

18 - 10 AWG

Voltage

125.0 V

---