



Turnlok® Receptacle Single 3-Wire 30A 125A

## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007253054	Country Of Origin	Mexico
Application Sector	Industrial	Standard	UL 498, FEDSPEC

### Dimensions

Product Width US	1.61 in	Product Depth US	1.28 in
Product Height US	2.37 in		

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Number of Wires	3	Amperage	30 A
Number of Poles	Double Pole	Wire Size	4 AWG
Voltage	125.0 V		