



Pass and Seymour  
30A NEMA L630 Flanged Inlet, Gray  
Part No. L630FI



Turnlok® Flanged Inlet, 3-Wire 30A 250V

## Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007263022	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL 498

### Dimensions

Product Width US	3.12 in	Product Depth US	1.75 in
------------------	---------	------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	146159	cULus Listed	Yes
---------------------	--------	--------------	-----

### Technical Information

Phase	Three	Number of Wires	3
Amperage	30 A	Number of Poles	Double Pole

---

Wire Size

18 - 10 AWG

---