

Flanged Outlet 3-Wire 20A 277V Turnlok®



Features & Benefits

Interior components constructed of high-grade brass material for physical and electrical integrity. High-impact thermoplastic housing withstands on-the-job abuse.

Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Specifications

General Info

| | | | |
|-------------------|----------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL 498 | | |

Dimensions

| | | | |
|------------------|---------|------------------|---------|
| Product Width US | 2.87 in | Product Depth US | 1.34 in |
|------------------|---------|------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|-----------------|-------|
| CSA Listed | Yes | CSA File Number | 16063 |
|------------|-----|-----------------|-------|

Technical Information

| | | | |
|----------|------|-----------------|-------------|
| Phase | 3 | Number of Wires | 3 |
| Amperage | 20 A | Wire Size | 18 - 10 AWG |

Voltage

277.0 V
