

Turnlok® Single Receptacle, 3-Wire 30A 277V



## Features & Benefits

Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.

One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.

Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.

Accepts #14 - #10 AWG.

Face color coding by voltage facilitates locating and mating of proper devices.

Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.

Side and external screw-pressure-plate back wire capability.

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial     | Standard          | UL 498 |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.61 in | Product Depth US | 1.28 in |
| Product Height US | 2.42 in |                  |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Additional Information

---

Product Environmental Profile      Yes

---

### Technical Information

---

|           |             |                 |             |
|-----------|-------------|-----------------|-------------|
| Phase     | 3           | Number of Wires | 3           |
| Amperage  | 30 A        | Number of Poles | Double Pole |
| Wire Size | 18 - 10 AWG | Voltage         | 277.0 V     |

---