



Wattstopper  
1/2 KO DLM cable connector for LMFC fixture integrated  
Part No. LMFC-RJ-50-24



The LMFC-xRJ provides fixture connectivity to the DLM local network via a single- or dual-port RJ45 wiring whip connector. The dual-port is best for daisy chaining multiple fixtures together. Each DLM local network can support up to 64 loads.

## Features & Benefits

Separate single- or dual-port RJ45 connector mounts on fixture housing, and provides connectivity to DLM local network

## Specifications

### General Info

Product Line	Wattstopper	Color	Gray
UPC Number	754182938957	Country Of Origin	China
Product Series	LMFC	Features	Flame Retardant, Impact Resistant, UV Grade
Installation Location	Fixture	Works With	DLM Fixture Controller
Application Sector	Commercial	Standard	UL, cUL, RoHS
Warranty Type	5-Year	Type	Interface

### Dimensions

Product Width US	1.3 in	Product Weight US	0.1 lb
Product Volume US	2.7 cu in	Product Depth US	1.6 in
Product Height US	1.3 in		

### Additional Information

RoHS Compliant	Yes
----------------	-----

---

Technical Information

Operating Temperature Min	32 °F	Number of Connections	1
Operating Temperature Max	158 °F	Indoor/Outdoor	Indoor
Mounting Type	1/2 in Knockout	Connector 1	RJ-45 Male
Operating Temperature	0°-70°C, 32°-158°F	Operating Humidity	5-95% RH (Non-Condensing)

---