



Wattstopper
LARGE NETWORK ENCLOSURE w/2NB-ROUTER 8-PORT SWITCH
Part No. LMNC-2-8



The LMNC is a surface-mount NEMA1-rated enclosure with DIN rails for mounting DLM network components. Comes with hinged cover and provided empty (LMNC-MT) or with 1–9 installed routers. Based on the catalog number suffix, a specific number of NB-ROUTERS and an NB-SWITCH can be installed in the panel and pre-wired to a power supply. Two single outlets are provided on the power supply, one for connecting an LMJA-8xxx-SM plug-in power supply, and a convenience outlet for a laptop or other technician required components.

Features & Benefits

NEMA1-rated enclosure

DIN rail mounting for easy installation or removal of LMJA-8xxx-SM (ordered separately)

Includes selection of pre-wired NB-ROUTERS and NB-SWITCH

Single termination point for one 120VAC circuit to power all devices

Power supply with two 120V outlets for Network Controller power and laptop or other set up tools

Specifications

General Info

Product Line	Wattstopper	Color	Gray
Finish	Glossy, Painted	UPC Number	754182943814
Country Of Origin	United States	Product Series	LMNC
Included	2 Routers, 8 Network Ports, Data Cables, DIN Rails, Hinged Door, Power Supply, Power Wiring	Number of Knockouts	1
Application Sector	Commercial	Standard	UL, ANSI 61
Warranty Type	5-Year	Type	Enclosure

Dimensions

Product Width US	16.0 in	Product Depth US	8.5 in
------------------	---------	------------------	--------

Product Height US	20.0 in	Knockout Size	1 in
-------------------	---------	---------------	------

Technical Information

Compatibility	DLM Wired	Power Supply	120 - 24VAC
Gauge	14	Enclosure Type	NEMA 1, Network
Configuration	With Router and Switch	Input Voltage	120 VAC
Line Frequency	50 Hz, 60 Hz	Cable Entry	Knockout
Mounting Type	Screw Mount	Mounting	Wall