



Wattstopper
RJ45 Cables, 15 feet, plenum rated Green
Part No. LMRJ-P15



LMRJ Series cables connect Digital Lighting Management (DLM) components without the need for tools or point-to-point discrete wiring. Cables are pre-terminated with industry standard RJ45 connectors compatible with any RJ45 port on DLM components. LMRJ cables utilize B to B wiring.

Features & Benefits

Pre-terminated LMRJ cables for DLM local networks in lengths up to 100 feet

UL and cUL listed and labeled

Wattstopper LM-MSTP wire required for wired segment networks.

This wire is not needed for wireless DLM networks using the wireless bridge (LMBC-600)

Standard green color and markings for DLM provide easy identification of LMRJ cables in plenum

Cables and wire available in a choice of colors for use in exposed locations

LMRJ cables available in plenum and non-plenum rating

Specifications

General Info

Product Line	Wattstopper	Color	Green
UPC Number	754182925162	Country Of Origin	China
Product Series	LMRJ	Jacket Color	Green with Black Stripe
Application Sector	Commercial	Standard	UL, cUL, PEP
Warranty Type	5-Year	Type	Cable

Dimensions

Product Weight US	0.3 lb	Product Volume US	54.0 cu in
Product Depth US	0.5 in	Product Height US	0.6 in

Product Length US	180.0 in	Cable Length	15 ft
Technical Information			
Jacket Material	PVC	Category Performance Rating	Cat5e
Wire Gauge	24 AWG	Jacket Application	Plenum Rated
Shielded/Unshielded	Unshielded	Termination Style	Pre-Terminated
Conductor	4-Pair Twisted	Cable Type	Booted, Snagless
Jacket Rating	FT6 Rated	Temperature Rating	75° C
Cable Diameter	0.2 in	Indoor/Outdoor	Indoor
Insulation Material	FEP (Fluorinated Ethylene Propylene)		