



Pass and Seymour
Discontinued - LS Series Incandescent Slide Dimmer, Ivory | Sub LS600I
Part No. LS1000I

Incandescent Slide Dimmer, Non-Preset 1000W, Ivory



Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see www.legrand.us/patents.

Electromagnetic and radio-frequency interference protection built in.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	LS600I
Color	Ivory	Country Of Origin	China
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Operating Cycles	100000	Amperage	8.3 A
Number of Poles	Single Pole	Wattage	1000 W
Voltage	120.0 V	Load	1000 Watt
