



Pass and Seymour  
**Discontinued - LS Series Incandescent Slide Dimmer, Ivory**  
Part No. LS600I

Incandescent Slide Dimmer, Preset 600W



## Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

No derating on 600W units.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Electromagnetic and radio-frequency interference protection built in.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Superior heat management.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Residential
Standard	UL Listed	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

### Technical Information

Operating Cycles	100000	Number of Poles	Single Pole
Wattage	600 W	Voltage	120.0 V
Load	600 Watt		