

Incandescent Slide Dimmer, Preset 600W



## Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Superior heat management.

No derating on 600W units.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Replaced by Part Number	LSCL453PBK
Color	Black	Country Of Origin	China
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

### Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

---

### Technical Information

---

Operating Cycles	100000	Number of Poles	Single Pole
------------------	--------	-----------------	-------------

---

Wattage	600 W	Voltage	120.0 V
---------	-------	---------	---------

---

Load	600 Watt
------	----------

---