



Pass and Seymour  
LS Series CFL/LED/Incandescent 3-Way Slide Dimmer, Non-Preset, Black  
Part No. LSCL453PBK



Works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)	Single pole/3-way versions
Unique integrated single pole/3-way dimmer control	Rating: 450W LED & CFL: 700W Incandescent: 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007040364
Country Of Origin	China	Product Series	Trademaster
Features	Low-End Trim (Dim Range)	Switch Type	Rocker, Single Pole 3-Way, Slider
Number of Switches	1	Application Sector	Residential
Standard	cULus, RoHS	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
------------------	---------	------------------	---------

Product Height US	4.19 in
-------------------	---------

Technical Information

Preset	Yes	Load Rating	120V 4.5A 450W (CFL), 120V 4.5A 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Screw Terminals
Voltage	120 VAC	Load Type	CFL, Halogen, Incandescent, LED
Environmental Conditions	Humidity: Less than 95% non condensing		