



Pass and Seymour

LS Series CFL/LED/Incandescent Single Pole/3-Way Slide Dimmer with Single Pole/3-Way, 3-Speed De-Hummer Fan Control, Preset, White
Part No. LSCLDC163PWCCV4



The industry's first CFL/LED dimmer with fan speed control works with select dimmable CFL/LED or incandescent lighting loads and features a sleek, sculpted ergonomic design for smooth, easy operation and precise control.

Features & Benefits

CFL/LED dimmable bulb compatible (except for 0-10V LED drivers)

Single pole/3-way versions

Unique integrated single pole/3-way dimmer with fan speed control

Ratings: 150W LED & CFL: 300W Incandescent: 1.6A (Fan Control): 120VAC 60Hz

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007040579
Country Of Origin	China	Material	Steel, Thermoplastic
Product Series	Trademaster	Features	Combination, De-Hummer Fan Control, Low-End Trim (Dim Range)
Switch Type	Rocker, Slider	Number of Switches	2
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty

Dimensions

Product Width US	2.5 in	Product Depth US	1.28 in
Product Height US	4.19 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Preset	Yes	Load Rating	120V 1.25A 150W (CFL), 120V 1.25A 150W (LED), 120V 1.6A (FAN MOTOR), 120V 300W (Halogen), 120V 300W (Incandescent)
Dimming Compatibility	Forward Phase	Frequency Rating	60 Hz
Number of Poles	Single Pole 3-Way	Wire Size	#14 - #10 AWG
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Wire Connection Type	Flying Leads
Voltage	120 VAC	Load Type	CFL, Fan Motor, Halogen, Incandescent, LED