



Pass and Seymour
Discontinued - LS Series Low-Voltage Slide Dimmer, Black
Part No. LSLV600PBK

Magnetic Low-Voltage Slide Dimmer, Preset 600VA



Features & Benefits

Ergonomic design and solid, quality feel combine for smooth, easy operation and precise Electromagnetic and radio-frequency interference protection built in. control.

Sleek, sculpted contemporary design. No dirt-catching crevices.

Tough, impact-resistant thermoplastic housing makes it a perfect choice for new home construction. Matching, unbreakable TradeMaster wall plate available for all models.

Preset ON/OFF switch automatically returns controlled lights to preset level without readjusting dimmer setting.

Exclusive, screw-pressure-plate back wire terminals save time, space and money. Designed for 12 and 14 gauge wire, stranded or solid. No-wire-lead design eliminates wire nuts.

Superior heat management.

No derating on 600W units.

Patented Snap-In Light Module (sold separately) transforms the dimmer into an illuminated dimmer.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007045628	Country Of Origin	China
Application Sector	Commercial, Residential	Standard	UL/CSA Listed
Type	Dimmer		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	95219	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Operating Cycles	100000	Number of Poles	Single Pole
Wattage	600 W		
