



Pass and Seymour
LS Series Fan Speed Control, Brown
Part No. LSSC5

Decorator Slide Fan Control, Preset/3-Speed/5A



Features & Benefits

Tough impact-resistant thermoplastic housing.

Power-failure memory.

Superior heat management: no time wasting break off tabs.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Can be used with patented Snap-In Light Module (sold separately).

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007277630
Country Of Origin	China	Features	Fan Control
Application Sector	Residential	Standard	UL Listed
Type	Dimmer		

Dimensions

Product Width US	1.74 in	Product Depth US	1.28 in
Product Height US	4.185 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes		
Technical Information			
Operating Cycles	100000	Amperage	5 A
Number of Poles	Single Pole	Wire Size	#14 - #10 AWG
Mounting Type	Box		