

Decorator Slide Fan Control, Preset/3-Speed/5amp, Brown



Features & Benefits

Tough impact-resistant thermoplastic housing.

Superior heat management: no time wasting break off tabs.

Can be used with patented Snap-In Light Module (sold separately).

Power-failure memory.

Exclusive screw-pressure-plate back wire terminals eliminates wire nuts.

Specifications

General Info

Color Ivory

UPC Number 785007158120

Country Of Origin China

Product Line Pass & Seymour

Application Sector Residential

Type Dimmer

Standard UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Number of Poles Single Pole

Voltage 120 V

Operating Cycles 100000