



C2G
UPS, Online, LCD, 1000VA, 120V, 2U, (8) 5-15R, 5-15P Cord
Part No. LU-1000-RT



Protect mission critical hardware in IT closets, voice and data networks, unmanned facilities, light industrial, and financial branches through double-conversion online power protection. Multiply the reach and ability of IT staff and caretakers through a single portal, providing visibility and control of power usage and available capacity, simplifying maintenance responsibilities for taxed IT departments.

Features & Benefits

- Zero Transfer Time: Seamless transfer of power from AC to battery and inverter to bypass
- Pure Sinewave Output: Provides the ideal waveform for the most sensitive equipment
- Input Power Factor Correction: Optimized and ideal efficiency at full load
- Designed to Work in Tandem with a Generator: Ensures smooth transition to generators during longer outages
- 4-Post Rack Mounting Kit: Included for simplified rack mounting
- True Double-Conversion: Provides the highest protection from raw input power (surges, spikes, and dips)
- Wide Input Voltage Range: Enables stable wide range application usage
- Programmable Outlet Bank: Ensures efficient and timely powering down of attached non-critical equipment
- Optional Remote Management Control: Provides visibility and control of power usage and availability, both on-site or at a remote unmanned facility
- Tower Mounting Option: Includes feet for non-rack applications, enabling the UPS to stand up by providing stability

Specifications

General Info

Product Line	TBD	Color	Black
UPC Number	662875016939	Country Of Origin	China
Application Sector	Commercial	Standard	UL 1783
Warranty Type	2-Year	Type	UPS (Uninterruptible Power Supply)

Technical Information

Rack Units	2 U	Plug Type	5-15P
------------	-----	-----------	-------

Wattage	1000 W	Mounting	Horizontal
Number of Outlets	8	Voltage	120.0 V
