



C2G
UPS, Online, LCD, 1000VA, 120V, 2U, (8) 5-15R, 5-15P Cord
Part No. LU-1000-RT



Protect mission critical hardware in IT closets, voice and data networks, unmanned facilities, light industrial, and financial branches through double-conversion online power protection. Multiply the reach and ability of IT staff and caretakers through a single portal, providing visibility and control of power usage and available capacity, simplifying maintenance responsibilities for taxed IT departments.

Features & Benefits

| | |
|--|--|
| Zero Transfer Time: Seamless transfer of power from AC to battery and inverter to bypass | True Double-Conversion: Provides the highest protection from raw input power (surges, spikes, and dips) |
| Pure Sinewave Output: Provides the ideal waveform for the most sensitive equipment | Wide Input Voltage Range: Enables stable wide range application usage |
| Input Power Factor Correction: Optimized and ideal efficiency at full load | Programmable Outlet Bank: Ensures efficient and timely powering down of attached non-critical equipment |
| Designed to Work in Tandem with a Generator: Ensures smooth transition to generators during longer outages | Optional Remote Management Control: Provides visibility and control of power usage and availability, both on-site or at a remote unmanned facility |
| 4-Post Rack Mounting Kit: Included for simplified rack mounting | Tower Mounting Option: Includes feet for non-rack applications, enabling the UPS to stand up by providing stability |

Specifications

General Info

| | | | |
|--------------------|--------------|-------------------|------------------------------------|
| Product Line | TBD | Color | Black |
| UPC Number | 662875016939 | Country Of Origin | China |
| Application Sector | Commercial | Standard | UL 1783 |
| Warranty Type | 2-Year | Type | UPS (Uninterruptible Power Supply) |

Technical Information

| | | | |
|------------|-----|-----------|-------|
| Rack Units | 2 U | Plug Type | 5-15P |
|------------|-----|-----------|-------|

| | | | |
|-------------------|--------|----------|------------|
| Wattage | 1000 W | Mounting | Horizontal |
| Number of Outlets | 8 | Voltage | 120.0 V |