



Infinium M4 Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2). Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

## Features & Benefits

Flexible Install: Mount from the front or the rear of an enclosure or panel	Installation Convenience: Do all splicing and managing work outside the enclosure
Clear Top: Enables fast and easy fault identification	Compact: These Splice cassettes provide a very compact splicing solution
Front or Rear Mounting: Simplify installation by mounting from the front or rear of the enclosure panel	Flexible Install: Mount from the front or rear of an enclosure or panel
Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager	

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875027010
Country Of Origin	China	Application Sector	Commercial
Warranty Type	5-Year	Type	Cassette

### Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

### Technical Information

Fiber Optic Cable Type	OS2	Compatibility	HDFP, LM4
Number of Ports	12	Simplex/Duplex	Duplex
Return Loss	65 dB	Single/Multimode	Single-Mode

---

Performance Level/Tier

Infinium Core

---