



Ortronics  
**12-FIBER OM4+ M4 CASSETTE WITH 12 LC DUPLEX ADAPTERS TO 1 MPO M- TIER 2- METHOD B- NEAR END**  
Part No. M4LCD12-50EC2A1



Infinium M4 pre-terminated cassettes with method B provide rapid deployment and have a flipped polarity inside the modules, which use key-up to key-up MPO adapters and allows for straight through patching. The rugged metal housing offers additional durability and includes a built-in internal bend limiting feature to assure optimum optical performance.

## Features & Benefits

Fully Compatible with Infinium INFC Enclosures  
4 Cassettes Fit into 1U  
Front Adapter Housing Colors Follow TIA/EIA-568.3-D Suggested Color Identification Scheme  
Each cassette has a data label with insertion loss value for each port

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875001027
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

### Additional Information

RoHS Compliant	Yes
----------------	-----