



Infinium M4 Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

Flexible Install: Mount from the front or the rear of an enclosure or panel	Installation Convenience: Do all splicing and managing work outside the enclosure
Clear Top: Enables fast and easy fault identification	Compact: These Splice cassettes provide a very compact splicing solution
Front or Rear Mounting: Simplify installation by mounting from the front or rear of the enclosure panel	Flexible Install: Mount from the front or rear of an enclosure or panel
Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager	

Specifications

General Info

Product Line	Ortronics	UPC Number	662875025597
Country Of Origin	United States	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----