



Infinium M4 Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

Flexible Install: Mount from the front or the rear of an enclosure or panel	Installation Convenience: Do all splicing and managing work outside the enclosure
Clear Top: Enables fast and easy fault identification	Compact: These Splice cassettes provide a very compact splicing solution
Front or Rear Mounting: Simplify installation by mounting from the front or rear of the enclosure panel	Flexible Install: Mount from the front or rear of an enclosure or panel
Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager	

Specifications

General Info

Product Line	Ortronics	Color	Black
UPC Number	662875025580	Country Of Origin	United States
Included	{12 or 24} Fiber Pigtails, Adapter Panel, Protective Dust Caps, Splice Management Tray, Splice Protection Sleeves	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Conformant Yes

Technical Information

Compatibility	Infinium HD-E / Infinium Panel	Number of Ports	24
Connector Type	LC Quad	Performance Level/Tier	Infinium Quantum
