



Ortronics
Infinium Quantum M4 Splice Cassette, 24 Single Fiber, LC Quad, OM4
Part No. M4LCQ24-50ES4A1

Infinium M4 Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24 fibers and are available in LC Duplex or LC Quad port configurations. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

Flexible Install: Mount from the front or the rear of an enclosure or panel

Installation Convenience: Do all splicing and managing work outside the enclosure

Clear Top: Enables fast and easy fault identification

Compact: These Splice cassettes provide a very compact splicing solution

Front or Rear Mounting: Simplify installation by mounting from the front or rear of the enclosure panel

Flexible Install: Mount from the front or rear of an enclosure or panel

Patented Splice Management: Simplify Splicing and fiber management outside of the cassette with the removable fiber splice manager

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875027133	Country Of Origin	Mexico
Application Sector	Commercial	Warranty Type	5-Year
Type	Cassette		

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Technical Information

Fiber Optic Cable Type	OM4	Compatibility	Infinium, M4
Number of Ports	24	Single/Multimode	Multimode

Performance Level/Tier

Infinium Quantum
