



Infinium M4 Cassettes are part of a complete fiber solution. When combined with matched Infinium Trunks and Infinium Patch Cable Assemblies the solution can enable industry leading pre-terminated performance and universal polarity for simple, fast and consistent and simplified installation. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

Premium performance cassette insertion loss: 0.50dB maximum

1.05dB total insertion loss for single-mode system

Standard performance cassette insertion loss: 0.75dB maximum

Insertion loss value for each port printed on adhesive data label

Specifications

General Info

Product Line	Ortronics	UPC Number	662875984344
Country Of Origin	China	Application Sector	Commercial
Standard	TIA-568-C.3	Type	Cassette

Dimensions

Product Width US	3.45 in	Product Depth US	4.77 in
Product Height US	1.14 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----