



Infinium M4 SC Splice Cassettes enable industry leading performance, fast field termination, and provide cable management within the housing. The Splice Cassettes are designed for use with Single-Mode (OS2) or Multimode (OM4/OM5) Fiber, Houses 12-24. Compatible with Infinium HD-E Rack Mount Fiber Enclosure with M4 Drawer Face.

Features & Benefits

- Mounts from either the front or rear of the enclosure or panel
- Tier 1 performance characteristics for insertion and return loss

Specifications

General Info

Product Line	Ortronics	Color	Aqua
UPC Number	662875027201	Country Of Origin	United States
Application Sector	Commercial	Warranty Type	5-Year
Type	Cassette		

Dimensions

Product Width US	4.19 in	Product Depth US	6.15 in
Product Height US	1.24 in		

Technical Information

Fiber Optic Cable Type	OM4	Compatibility	M4
Number of Ports	12	Simplex/Duplex	Duplex
Return Loss	40 dB	Single/Multimode	Multimode
Performance Level/Tier	Infinium Quantum		