



Wiremold  
Plug-In Outlet Center Unit / 120V/20A/6 O/L /lighted switch/15' cord/Computer Grade Surge  
Part No. M620BZLS-15



Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 20A. 15' (4.6m) 12/3 SJT putty white cord with NEMA5-15 plug. Length 18" (457mm). Snap-on, slide-off mounting.

## Features & Benefits

Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 20A. 15' (4.6m) 12/3 SJT putty white cord with NEMA5-15 plug. Length 18" (457mm). Snap-on, slide-off mounting.

## Specifications

### General Info

|                   |   |                    |                        |
|-------------------|---|--------------------|------------------------|
| Product Line      | Wiremold  | UPC Number         | 786776524130           |
| Country Of Origin | Mexico  | Application Sector | Residential/Commercial |
| Standard          | cULus Listed: File E66421 Guide XYBS XUHT<br>VZCA | Type               | PIOC                   |

### Dimensions

|                   |         |                   |         |
|-------------------|---------|-------------------|---------|
| Product Width US  | 18.0 in | Product Height US | 1.89 in |
| Product Length US | 2.0 in  |                   |         |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Buy American Act Compliance

|       |     |
|-------|-----|
| NAFTA | Yes |
|-------|-----|

### Technical Information

|            |              |                  |          |
|------------|--------------|------------------|----------|
| Phase      | Single Stage | Frequency Rating | +35dB Hz |
| Connection | Cord-ended   | Class            | 75       |

---

|               |         |                          |   |
|---------------|---------|--------------------------|---|
| Amperage      | 20 A    | Short Circuit Rating     | 36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G] |
| Response Time | <1 ns   | Mounting Type            | Snap-on, Slide-off  |
| Mounting      | Yes     | Type of Indicators       | Light   |
| Voltage       | 120.0 V | Environmental Conditions | Indoor, dry location                                      |

---