



Wiremold
Plug-In Outlet Center Unit / 120V/20A/6 O/L /lighted switch/15' cord/Computer Grade Surge
Part No. M620BZLS-15



Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 20A. 15' (4.6m) 12/3 SJT putty white cord with NEMA5-20 plug. Length 18" (457mm). Snap-on, slide-off mounting.

Features & Benefits

Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 20A. 15' (4.6m) 12/3 SJT putty white cord with NEMA5-20 plug. Length 18" (457mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	Color	Bronze
UPC Number	786776524130	Country Of Origin	Mexico
Product Series	Perma Power	Number of Receptacles	6
Features	Lighted Switch, Surge Protection	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	18.0 in	Product Weight US	4.0 lb
Product Height US	1.89 in	Product Length US	2.0 in
Receptacle Spacing	1.5 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Technical Information

Phase	Single Stage	Cord Length	15 ft
Connection	Cord-ended	Class	75
Amperage	20 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Indoor/Outdoor	Indoor
Wiring Method	Cord-ended	NEMA Configuration Code	5-20P, 5-20R
Mounting Type	Snap-on, Slide-off	Location Rating	Dry
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V	Environmental Conditions	Indoor, dry location
