



Wiremold
Plug-In Outlet Center Unit / 120V/15A/6 O/L /lighted switch/15' cord/Computer Grade Surge
Part No. M6BZ-15



Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 16" (407mm). Snap-on, slide-off mounting.

Features & Benefits

Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 16" (407mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	UPC Number	786776043150
Country Of Origin	Mexico	Application Sector	Residential/Commercial
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Type	PIOC

Dimensions

Product Width US	13.75 in	Product Height US	1.89 in
Product Length US	2.0 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Technical Information

Phase	Single Stage	Frequency Rating	+35dB Hz
Connection	Cord-ended	Class	75

Amperage	15 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Mounting Type	Snap-on, Slide-off
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V	Environmental Conditions	Indoor, dry location
