



Wiremold
Plug-In Outlet Center Unit / 120V/15A/6 O/L /lighted switch/15' cord/Computer Grade Surge
Part No. M6BZ-15



Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 16" (407mm). Snap-on, slide-off mounting.

Features & Benefits

Perma Power computer grade surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 16" (407mm). Snap-on, slide-off mounting.

Specifications

General Info

| | | | |
|----------------|--|-----------------------|--|
| Product Line | Wiremold | Color | Bronze |
| UPC Number | 786776043150 | Country Of Origin | Mexico |
| Product Series | Perma Power | Number of Receptacles | 6 |
| Features | Lighted Switch, Surge Protection | Application Sector | Commercial, Residential |
| Standard | cULus Listed: File E66421 Guide XYBS XUHT VZCA | Warranty Type | 1-Year from Installation or 2-Years from Day of Sale |
| Type | PIOC | | |

Dimensions

| | | | |
|--------------------|----------|-------------------|---------|
| Product Width US | 13.75 in | Product Weight US | 3.25 lb |
| Product Height US | 1.89 in | Product Length US | 2.0 in |
| Receptacle Spacing | 1.25 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | E66421 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Trade Programs

| | |
|-------|-----|
| USMCA | Yes |
|-------|-----|

Technical Information

| | | | |
|---------------|--------------------|--------------------------|---|
| Phase | Single Stage | Cord Length | 15 ft |
| Connection | Cord-ended | Class | 75 |
| Amperage | 15 A | Short Circuit Rating | 36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G] |
| Response Time | <1 ns | Indoor/Outdoor | Indoor |
| Wiring Method | Cord-ended | NEMA Configuration Code | 5-15P, 5-15R |
| Mounting Type | Snap-on, Slide-off | Location Rating | Dry |
| Mounting | Yes | Type of Indicators | Light |
| Voltage | 120.0 V | Environmental Conditions | Indoor, dry location |
