



## Wiremold

**Plug-In Outlet Center Unit / 120V/15A/6 O/L /remote lighted switch/15' cord/Computer Grade Surge**  
Part No. M6BZR-15



Perma Power computer grade surge protection. Six outlets, remote switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 13 1/4" (337mm). Snap-on, slide-off mounting.

### Features & Benefits

Perma Power computer grade surge protection. Six outlets, remote switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 13 1/4" (337mm). Snap-on, slide-off mounting.

### Specifications

#### General Info

Product Line	Wiremold	Color	Bronze
UPC Number	786776047752	Country Of Origin	Mexico
Product Series	Perma Power	Number of Receptacles	6
Features	Remote Switch, Surge Protection	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

#### Dimensions

Product Width US	13.75 in	Product Weight US	4.0 lb
Product Height US	1.89 in	Product Length US	2.0 in
Receptacle Spacing	1.25 in		

#### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

#### Trade Programs

USMCA	Yes
-------	-----

---

## Technical Information

---

Phase	Single Stage	Cord Length	15 ft
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	36000 Amps [12000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Indoor/Outdoor	Indoor
Wiring Method	Cord-ended	NEMA Configuration Code	5-15P, 5-15R
Mounting Type	Snap-on, Slide-off	Location Rating	Dry
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V	Environmental Conditions	Indoor, dry location

---