



Wiremold
Plug-In Outlet Center Unit / 120V/15A/6 O/L /lighted switch/15' cord/Premium Grade Surge
Part No. M6S-15



Sentrex high performance surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 15 1/4" (387mm). Snap-on, slide-off mounting.

Features & Benefits

Sentrex high performance surge protection. Six outlets, lighted switch, durable putty white aluminum housing, 15A. 15' (4.6m) 14/3 SJT putty white cord with NEMA5-15 plug. Length 15 1/4" (387mm). Snap-on, slide-off mounting.

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786776043242	Country Of Origin	Mexico
Product Series	Sentrex	Number of Receptacles	6
Features	Lighted Switch, Surge Protection	Application Sector	Commercial, Residential
Standard	cULus Listed: File E66421 Guide XYBS XUHT VZCA	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	PIOC		

Dimensions

Product Width US	15.25 in	Product Weight US	4.0 lb
Product Height US	1.89 in	Product Length US	2.0 in
Receptacle Spacing	1.25 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E66421	cULus Listed	Yes
---------------------	--------	--------------	-----

Trade Programs

USMCA	Yes
-------	-----

Technical Information

Phase	3 Element, 3-Stage Hybrid Circuit	Cord Length	15 ft
Connection	Cord-ended	Class	75
Amperage	15 A	Short Circuit Rating	56000 Amps [32000 Amps L-N 12000 Amps L-G 12000 Amps N-G]
Response Time	<1 ns	Indoor/Outdoor	Indoor
Wiring Method	Cord-ended	NEMA Configuration Code	5-15P, 5-15R
Mounting Type	Snap-on, Slide-off	Location Rating	Dry
Mounting	Yes	Type of Indicators	Light
Voltage	120.0 V	Environmental Conditions	Indoor, dry location
